



PGMF1300

Voltage supply cable

Technical Features

Architecture

Number of poles 4

Voltage

Max. operating voltage 230 V

Cable

Cable length 1.30 m

Dimensions

Length 1300 mm

Equipment

Mechanical coding No

Type cable side 1 Free conductor end

Type of cable Device connection cable

Materials

Colour Green

Sustainability

REACH-SVHC free Yes

RoHS conform Yes