



FL279B

Polyester enclosure, Orion.Plus, glazed door 800x600x300 mm

Technical Features

Dimensions

Height	800 mm
Width	600 mm
Depth	300 mm
Thickness of sidewall	3 mm

Safety

Ingress Protection (IP) class	IP66
Protection class	Isolation class II
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK08

Equipment

Number of flange plate openings	0
---------------------------------	---

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

Equipment

Number of rows	5
----------------	---

Cover, door

Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	Yes
Cabinet door type	Single door

Electric current

Rated current	125 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----