



BF241N

Earth leakage add-on block 2P 40A 300mA AC Class

Technical Features

Architecture

| | |
|------------------|-------|
| Neutral position | Right |
| Number of poles | 2 |

Capacity

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Voltage

| | |
|---|-------------|
| Rated operational voltage U_e | 230 - 400 V |
| Rated insulation voltage U_i | 500 V |
| Rated impulse withstand voltage U_{imp} | 4000 V |

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Electric current

| | |
|---|--------|
| Rated residual operating current I_{dn} | 300 mA |
| Rated current | 40 A |

Connectivity

| | |
|---|------------------|
| Down connection alignment for modular devices | Aligned terminal |
|---|------------------|

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 35 mm |
| Depth | 92 mm |