



EE101

#### Light sensitive switch

##### Technical Features

###### Frequency

Frequency	50 - 50 Hz
-----------	------------

###### Voltage

Rated operational voltage Ue	230 - 230 V
------------------------------	-------------

###### Settings

Switch on delay time	0 s
----------------------	-----

##### Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

Storage/transport temperature	-20 - 60 °C
-------------------------------	-------------

##### Connection

Cross-section flexible conductor	0.5 - 4 mm <sup>2</sup>
----------------------------------	-------------------------

Cross-section rigid conductor	0.5 - 4 mm <sup>2</sup>
-------------------------------	-------------------------

##### Capacity

Number of modules	3
-------------------	---

##### Dimensions

Height	88.50 mm
--------	----------

Width	53 mm
-------	-------

Depth	65 mm
-------	-------