



MH2503S4

**MCCB Enclosure, 250A MCCB incomer, 3 way, Malta**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No

**Voltage**

Nominal voltage	415 - 415 V
-----------------	-------------

**Electric current**

Rated current	250 A
---------------	-------

**Dimensions**

Depth	122 mm
Internal depth	117 mm
Height	466 mm
Width	296 mm
Thickness of sidewall	1.20 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9002
Colour	Grey white
Material	Steel

**Connection**

Number of conduit inlets	10
--------------------------	----

**Equipment**

Number of rails	0
Extension possible	No
With bell transformer	No
With socket outlet	No

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP20
Protection class	Isolation class I

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes