



16216074

Rocker w. 2 lenses attached and imprinted light symbol, Q.x, alu velvety, lacq.

Technical Features

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Materials

| | |
|----------------|-------------|
| Colour | Aluminium |
| RAL code | 9006 |
| Surface finish | Velvety |
| Material | Duroplastic |
| Treatment | Varnished |

Dimensions

| | |
|--------|-------|
| Height | 52 mm |
| Width | 52 mm |
| Depth | 23 mm |

Connectivity

| | |
|---------------|----------------|
| Mounting type | Clamp mounting |
|---------------|----------------|

Equipment

| | |
|--------------------------------|-----|
| Monitoring window/light outlet | Yes |
|--------------------------------|-----|

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK | IK02 |

Texts

| | |
|----------------------------------|-------------------------------------------------------------------------------|
| Imprint | With imprinted symbol light |
| Installation mode | Clamp fastening |
| Lighting | For lighting and monitoring circuit |
| Push button | Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang |
| Rocker switch/rocker push-button | For rocker push-buttons For change-over/intermediate switch |

Suitable for

| | |
|-----|--|
| Q.x | |
|-----|--|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |