



936752501



Series push-button, 2 NO cont com input term, Integro - Design Flow/Pure, br m

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Double push button
Number of poles	2

Materials

Colour	Brown
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	55.50 mm
Width	55.50 mm
Depth	25 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

Controls and indicators

Number of buttons	2
Type of push button	Series push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Terminal	Common input terminal
Type of connection	With screw terminals

Suitable for

integro	
---------	--

Sustainability

RoHS conform	Yes
--------------	-----