



WGDL111EIG

10A 1G press switch mark "exit";ig

Technical Features

Electric current	
Switching current	10 A

Voltage	
Rated voltage	250 V

Architecture	
Control/operation element	Single rocker

Materials	
Colour	Interstellar grey
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Transparent	No

Dimensions	
Height	86 mm
Width	86 mm
Depth	25 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting	
Mounting on	Flush mounting

Controls and indicators	
Number of buttons	1
With feedback signal contact	No

Connectivity	
Type of connection	Screw terminal

Safety	
Ingress Protection (IP) class	IP20

Accessories	
Has labelling field	No

Texts	
Imprint	With imprint " " and symbol key
Switch mode	1-way

Suitable for	
shark	

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes