



VML\_SIZE\_2

**2 Way Garage Consumer Unit 40A 30mA Type A RCCB**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Has protection main switch	Yes
----------------------------	-----

Overvoltage protection	No
------------------------	----

**Capacity**

Number of modules	4
-------------------	---

**Electric current**

Rated current	40 A
---------------	------

**Dimensions**

Depth	98.20 mm
-------	----------

Height	245 mm
--------	--------

Width	225 mm
-------	--------

Number of width units	2
-----------------------	---

**Cover, door**

Interlockable	No
---------------	----

Door/cover is transparent	No
---------------------------	----

**Materials**

Colour	Pure white
--------	------------

Material	Steel
----------	-------

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	1
-----------------------------	---

**Safety**

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----