



FL52S

enclosure, univers, IP65, CL 2, 850 x 600 x 300mm, Polyester

Technical Features

Dimensions

Height	850 mm
Width	600 mm
Depth	300 mm
Thickness of sidewall	2 mm

Safety

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	3-point lever 4-side 8 mm
Impact resistance IK	IK10

Equipment

Number of section in width	2
Number of flange plate openings	0

Installation, mounting

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

Materials

Colour	Light grey
RAL code	7035
Treatment	Varnished
Material	Glass reinforced polyester

Equipment

Number of rows	5
----------------	---

Materials

Surface finish	Matt
----------------	------

Cover, door

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	No

Electric current

Rated current	400 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----