



EE110



Twilight switch, daily cycle

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Settings

Switch on delay time	15 s
----------------------	------

Use conditions

Operating temperature	-10 - 50 °C
Storage/transport temperature	-20 - 60 °C

Connection

Cross-section flexible conductor	0.5 - 4 mm ²
Cross-section rigid conductor	0.5 - 4 mm ²

Capacity

Number of modules	5
-------------------	---

Texts

Installation mode	For mounting on DIN rail Extension sensor for wall and ceiling mounting
Type of connection	With screw terminals

Dimensions

Height	85 mm
Width	88 mm
Depth	65 mm