



LNH0050M

HRC LV fuse NH000 gG AC500V 50A double indicator with live gripping-lugs

Technical Features

Architecture

Curve gG

Fuse

Fuse size NH000

Fuse characteristics gG

Voltage

Type voltage supply AC/DC

Rated operational voltage U_e 500 - 500 V

Rated voltage at AC 50 Hz 500 - 500 V

Electric current

Rated current 50 A

Use conditions

Insulated No

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1 120 kA

Power

Total power loss under I_N 4.10 W

Dimensions

Height 58.50 mm

Width 21 mm

Depth 79 mm

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes