



FL259B

### Polyester enclosure, Orion.Plus, glazed door 500x300x200 mm

#### Technical Features

##### Dimensions

Height	500 mm
Width	300 mm
Depth	200 mm
Thickness of sidewall	3 mm

##### Safety

Ingress Protection (IP) class	IP66
Protection class	Isolation class II
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK08

##### Equipment

Number of flange plate openings	0
---------------------------------	---

##### Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

##### Materials

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

##### Equipment

Number of rows	3
----------------	---

##### Cover, door

Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	Yes

##### Electric current

Rated current	125 A
---------------	-------

##### Sustainability

RoHS conform	Yes
--------------	-----