



WMCS3PIF

**10A 3P Ceiling Switch Marked FAN & ISOLATOR**

**Technical Features**

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Materials**

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

**Identification**

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Controls and indicators**

Number of buttons	0
-------------------	---

**Dimensions**

Dimensions	86 x 86 mm
Built-in depth	23 mm

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Pull cord
---------------------------	-----------

**Electric current**

Rated current	10 A
---------------	------

**Texts**

Lighting	Without lighting (cannot be illuminated)
Switch mode	3-pole

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes