Product Datasheet
FL254B



FL254B

Polyester enclosure, Orion.Plus, glazed door 350x300x160 mm

Technical Features

Dimensions	
Height	350 mm
Width	300 mm
Depth	160 mm
Thickness of sidewall	3 mm

Safety	
Ingress Protection (IP) class	IP66
Protection class	Isolation class II
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK08

Equipment	
Number of flange plate openings	0

Installation, mounting	
Mounting on	Surface mounting
Suitable for outdoor usage	Yes

Materials	
Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

Equipment	
Number of rows	2

Cover, door	
Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	Yes

Electric current	
Rated current	125 A

Sustainability	
RoHS conform	Yes