



WMCS11

6A Ceiling Switch 1 Way

Technical Features

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour White

Surface finish Glossy

Material Urea formaldehyde

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 0

Dimensions

Dimensions 86 x 86 mm

Built-in depth 0 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Pull cord

Electric current

Rated current 6 A

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 1-way

Sustainability

RoHS conform Yes