



WGDHSLNB

**sleeping light;nb**

**Technical Features**

**Voltage**

Rated voltage	230 V
---------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Lighting**

Type of lamp	LED
--------------	-----

**Materials**

Colour	Bronze
--------	--------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Coated
-----------	--------

**Dimensions**

Height	34 mm
--------	-------

Width	86 mm
-------	-------

Depth	34 mm
-------	-------

**Connection**

Conductor cross-section	0 - 1,5 mm <sup>2</sup>
-------------------------	-------------------------

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Suitable for**

shark	
-------	--

**Sustainability**

RoHS conform	Yes
--------------	-----