



WGDHSLIG

sleeping light;ig

Technical Features

**Voltage**

Rated voltage 230 V

**Frequency**

Frequency 50 - 60 Hz

**Lighting**

Type of lamp LED

**Materials**

Colour Interstellar grey

Surface finish Matt

Material Polycarbonate (PC)

Treatment Coated

**Dimensions**

Height 34 mm

Width 86 mm

Depth 34 mm

**Connection**

Conductor cross-section 0 - 1.5 mm<sup>2</sup>

**Connectivity**

Mounting type Screw mounting

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature -5 - 45 °C

**Suitable for**

shark

**Sustainability**

RoHS conform Yes