




WGDHSLKB

sleeping light;kb

Technical Features

Voltage

Rated voltage 230 V

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Knight black

Surface finish Matt

Material Polycarbonate (PC)

Treatment Coated

Dimensions

Height 34 mm

Width 86 mm

Depth 34 mm

Connection

Conductor cross-section 0 - 1.5 mm²

Connectivity

Mounting type Screw mounting

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5 - 45 °C

Suitable for

shark

Sustainability

RoHS conform Yes