

Technical Features

Dimensions

Installation height	2.20 - 2.20 m
Assembling height	31.40 mm

Detection

Type of sensor	Movement detector
Detection diameter on floor	0 - 0 m
Detection angle	180 - 180
Detection angle adjustable	180 - 180 °

Materials

Colour	Anthracite
Surface finish	Matt
Treatment	Untreated
Material	Thermoplastic

Reach distance

Max. transmission range frontally	12 m
Max. transmission range sideways	6 m

Settings

Response brightness adjustable	Yes
--------------------------------	-----

Use conditions

Operating temperature	-15 - 45 °C
-----------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Function	Dimming insert switch-off advance warning (30 s dimming process) With adaptive sensitivity adjustment Glare-proof, e.g. against a torch
Protection	With crawl-under protection