



WGDHSLEG

sleeping light;eg

Technical Features

Voltage

Rated voltage 230 V

Frequency

Frequency 50-60 Hz

Lighting

Type of lamp LED

Materials

Colour Gold

Surface finish Matt

Material Polycarbonate (PC)

Treatment Coated

Dimensions

Height 34 mm

Width 86 mm

Depth 34 mm

Connection

Conductor cross-section 0-1.5 mm<sup>2</sup>

Connectivity

Mounting type Screw mounting

Safety

Ingress Protection (IP) class IP20

Use conditions

Operating temperature -5-45 °C

Suitable for

shark

Sustainability

RoHS conform Yes