



30723505

On/off switch 2pole imprint "O" + "I" surface-mtd, W.1, grey/light grey matt

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Materials

Colour Grey

RAL code 7011

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 76 x 76 mm

Built-in depth 0 mm

Built-in depth flush-mounted boxes 0 mm

Safety

Ingress Protection (IP) class IP55

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Installation mode For screw fastening

Type of connection With N-terminal
With plug-in terminals

Switch mode 2x 1- -pole off