



30723505

### On/off switch 2pole imprint "O" + "I" surface-mtd, W.1, grey/light grey matt

#### Technical Features

##### Electric current

Switching current	10 A
-------------------	------

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

##### Identification

Assembly arrangement	Basic element with complete housing
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Dimensions	76 x 76 mm
Built-in depth	0 mm
Built-in depth flush-mounted boxes	0 mm

##### Safety

Ingress Protection (IP) class	IP55
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Electric current

Rated current	10 A
---------------	------

##### Texts

Installation mode	For screw fastening
Type of connection	With N-terminal With plug-in terminals
Switch mode	2x 1- -pole off