



47442089



## SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,R.cl

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Depth	51.50 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

#### Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	Yes
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	No
---------------------	----

#### Cover, door

Type of lid	Self-closing hinged cover
-------------	---------------------------

#### Capacity

Number of modules	1
-------------------	---

#### Safety

With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

<b>Functions</b>		
With orientation lighting		No
With function lighting		No
<b>Texts</b>		
Imprint		Without imprint
Cover		Central cover plate
Protection		Enhanced contact protection
Type of connection		With plug-in terminals
<b>Suitable for</b>		
R.x / Serie R.classic		
<b>Sustainability</b>		
Halogen free		Yes
RoHS conform		Yes