



WGDL131

16AX 3G 1W switch

Technical Features

<b>Electric current</b>	
Switching current	16 A
<b>Installation, mounting</b>	
Mounting on	Flush mounting
<b>Voltage</b>	
Rated voltage	250 V
<b>Frequency</b>	
Frequency	50-60 Hz
<b>Materials</b>	
Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
<b>Connectivity</b>	
Mounting type	Screw mounting
<b>Controls and indicators</b>	
Number of buttons	3
<b>Dimensions</b>	
Dimensions	86 x 86 mm
Built-in depth flush-mounted boxes	35 mm
<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Architecture</b>	
Control/operation element	Triple rocker
<b>Electric current</b>	
Rated current	16 A
<b>Texts</b>	
Lighting	Without lighting (cannot be illuminated)
Switch mode	1-way
<b>Sustainability</b>	
RoHS conform	Yes