



WGDL131

16AX 3G 1W switch

Technical Features

Electric current

Switching current 16 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 3

Dimensions

Dimensions 86 x 86 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Triple rocker

Electric current

Rated current 16 A

Texts

Lighting Without lighting (cannot be illuminated)

Switch mode 1-way

Sustainability

RoHS conform Yes