



47466086



**SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,Q.x,ant.**

#### Technical Features

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Voltage

|                 |             |
|-----------------|-------------|
| Rated voltage   | 250 V       |
| Nominal voltage | 250 - 250 V |

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

##### Materials

|                |               |
|----------------|---------------|
| Colour         | Anthracite    |
| RAL code       | 7021          |
| Surface finish | Velvety       |
| Material       | Thermoplastic |
| Treatment      | Varnished     |

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Height                             | 71 mm |
| Width                              | 71 mm |
| Number of units                    | 1     |
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth                     | 32 mm |

##### Connection

|                     |                  |
|---------------------|------------------|
| Connector/plug type | Plug-in terminal |
|---------------------|------------------|

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Connectivity

|                    |                                 |
|--------------------|---------------------------------|
| Type of connection | Plug-in connection              |
| Mounting type      | Screw mounting<br>Claw mounting |

##### Equipment

|                                   |        |
|-----------------------------------|--------|
| Connector/plug type socket outlet | SCHUKO |
| Rotated central insert            | No     |
| With hinged lid                   | Yes    |
| With round protective earth pin   | No     |
| With signal lamp                  | No     |
| With lock                         | No     |

##### Accessories

|                     |     |
|---------------------|-----|
| Has labelling field | Yes |
|---------------------|-----|

##### Cover, door

|             |                         |
|-------------|-------------------------|
| Type of lid | Hinged cover falls back |
|-------------|-------------------------|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Safety

|                                  |      |
|----------------------------------|------|
| With enhanced contact protection | Yes  |
| Impact resistance IK             | IK02 |
| Ingress Protection (IP) class    | IP20 |

##### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

|                    |                             |
|--------------------|-----------------------------|
| <b>Texts</b>       |                             |
| Imprint            | With imprint                |
| Cover              | Central cover plate         |
| Protection         | Enhanced contact protection |
| Type of connection | With plug-in terminals      |
| Labelling          | With labelling field        |

|                     |  |
|---------------------|--|
| <b>Suitable for</b> |  |
| Q.x                 |  |

|                       |     |
|-----------------------|-----|
| <b>Sustainability</b> |     |
| Halogen free          | Yes |
| RoHS conform          | Yes |