



WMPS12R

Push Switch

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Number of poles	2
-----------------	---

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Coated
Transparent	No

Dimensions

Height	86 mm
Width	86 mm
Depth	24 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Accessories

Has labelling field	No
---------------------	----

Texts

Imprint	Without imprint
Installation mode	For flush-mounted and hollow wall mounting
Switch mode	NO contact

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes