



SN010

Socket 16A Schuko + It

Technical Features

Electric current

Rated current	16 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Light grey
RAL code	7044
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Height	75 mm
Width	43.75 mm
Depth	61 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	DIN rail
-------------	----------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Capacity

Number of modules	2
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

Identification

With imprint	No
--------------	----

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

