



SN013

DIN socket 1xT13 screw terminal

Technical Features

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Light grey
RAL code	7035
Treatment	Varnished

Dimensions

Height	95 mm
Depth	22.80 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	DIN rail Mounting plate
-------------	----------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	Swiss norm type 13
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Capacity

Number of modules	3.50
-------------------	------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
---------------------------	----

Texts

Imprint	Without imprint
---------	-----------------

Sustainability

RoHS conform	Yes
--------------	-----