



SN013

DIN socket 1xT13 screw terminal

Technical Features

Electric current

Rated current 10 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Light grey

RAL code 7035

Treatment Varnished

Dimensions

Height 95 mm

Depth 22.80 mm

Built-in depth flush-mounted boxes 40 mm

Installation, mounting

Mounting on DIN rail
Mounting plate

Connectivity

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Swiss norm type 13

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Capacity

Number of modules 3.50

Safety

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

Identification

With imprint No

Sustainability

RoHS conform Yes