



11371404

Centre plate f. rot. dimmer/potentiometer, setting knob, B.7, al. matt lacq.

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Thermoplastic
Treatment	Varnished

Dimensions

Height	56 mm
Width	56 mm
Depth	16.30 mm
Diameter axis	4 mm

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Monitoring window/light outlet	No
--------------------------------	----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Imprint	Centre plate without imprint
Installation mode	For screw fastening

Suitable for

S.x/B.x	
---------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes