

#### Technical Features

##### Dimensions

Installation height	2.20 - 2.20 m
Assembling height	23.50 mm

##### Detection

Type of sensor	Movement detector
Detection diameter on floor	0 - 0 m
Detection angle	180 - 180
Detection angle adjustable	180 - 180 °

##### Materials

Colour	Polar white
Surface finish	Matt
Material	Thermoplastic

##### Reach distance

Max. transmission range frontally	12 m
Max. transmission range sideways	6 m

##### Lighting

Response brightness adjustable	0 - 80 lx
--------------------------------	-----------

##### Settings

Response brightness adjustable	Yes
--------------------------------	-----

##### Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Texts

Function	With adaptive sensitivity adjustment With dimming function (soft-off) when using BLC dimmer inserts Glare-proof, e.g. against a torch
----------	---