



WXPDP84N

IP66 20A 1 Gang 1 Way Double Pole Switch with Light Indicator

Technical Features

Installation, mounting

Mounting on Surface mounting

Voltage

Rated voltage 250 V

Materials

Colour Light grey

Surface finish Matt

Material Polycarbonate (PC)

Treatment Untreated

Identification

Assembly arrangement Basic element with complete housing

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 90 x 90 mm

Built-in depth 0 mm

Safety

Ingress Protection (IP) class IP66

Architecture

Control/operation element Single rocker

Electric current

Rated current 20 A

Texts

Lighting With control LED for ON

Switch mode 2-pole

Sustainability

REACH-SVHC free Yes

RoHS conform Yes