



TE332



Consumption Indicator KNX with current transformers

Technical Features

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Architecture

Bus system	KNX
------------	-----

Connectivity

With bus system Powernet	No
--------------------------	----

Electric current

Bus current consumption data transfer	15 mA
---------------------------------------	-------

Voltage

Operating voltage over bus	21 - 32 V
----------------------------	-----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Capacity

Number of modules	6
-------------------	---

Installation, mounting

Mounting on	DIN rail
-------------	----------

Texts

Terminal	With connecting terminal for outside temperature sensor With connecting terminal for remote communication input (only for France) With connecting terminal for tariff input (HT/NT) With mains connection terminals With 2 connecting terminals of the reference phases for counter channel 2 and 3 3x connecting terminals for current transformers
----------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Sustainability

RoHS conform	Yes
--------------	-----