



KJ125B

Brass busbar terminal 125A, 4pole, 1x 10-35<sup>2</sup> / 3x 6-35<sup>2</sup> / 11x 1,5-16<sup>2</sup> per pole

**Technical Features**

**Electric current**

Rated current 125 A

**Architecture**

Number of poles 4

**Dimensions**

Height 96 mm

Width 170 mm

Depth 64 mm

**Capacity**

Number of modules 10

**Installation, mounting**

Nominal tightening torque 2.50 - 2.50 Nm

**Sustainability**

Halogen free Yes

RoHS conform Yes