



LFR1501509010T2

**Mini flexible trunking on roll with adhesive tape LFR 15x15mm PVC in pure white**

**Technical Features**

**Dimensions**

Height	15 mm
Width	15 mm
Length	20000 mm
Inner cross-section	256 - 256 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	1
--	---

**Materials**

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9010
Colour	Pure white

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

**Standards**

Suitable for functional integrity according to DIN4102-12	No
---	----

**Use conditions**

Operating temperature	-5 - 60 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Without coupling
-------------------	------------------

**Equipment**

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	No
With protective film	No

**Illustrations | Drawings**

