



REQ510X



Door station VIDEO 10/1 2-wire stainless steel matt one

Technical Features

Materials

Surface finish	Matt
Material	Stainless steel

Controls and indicators

Number of call buttons	10
------------------------	----

Voltage

Operating voltage	24 - 24 V
-------------------	-----------

Dimensions

Dimensions	385.80 x 133.50 mm
Height	385.80 mm
Width	133.50 mm
Depth	25 mm
Camera dome diameter	33 mm

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

Functions

Door communication type	Audio + Video
-------------------------	---------------

Connection

Conductor cross-section	0 - 0 mm ²
-------------------------	-----------------------

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Texts

Installation mode	For vertical mounting Break-proof flush-mounted call buttons Installation in surface-mounted or flush-mounted housings
Junction	Pluggable connection terminal block with screw terminals
Lighting	Durable, homogeneous, white LED call push-button backlighting Invisible, glare-free IR LED night lighting
Protection	Loudspeaker and microphone protected against sabotage