



REQ516X



**Door station VIDEO 16/2 2-wire stainless steel matt one**

**Technical Features**

**Materials**

Surface finish	Matt
Material	Stainless steel

**Controls and indicators**

Number of call buttons	16
------------------------	----

**Voltage**

Operating voltage	24 - 24 V
-------------------	-----------

**Dimensions**

Dimensions	332 x 225.50 mm
Height	332 mm
Width	225.50 mm
Depth	25 mm
Camera dome diameter	33 mm

**Use conditions**

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

**Functions**

Door communication type	Audio + Video
-------------------------	---------------

**Connection**

Conductor cross-section	0 - 0 mm <sup>2</sup>
-------------------------	-----------------------

**Installation, mounting**

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

**Texts**

Installation mode	For vertical mounting Break-proof flush-mounted call buttons Installation in surface-mounted or flush-mounted housings
Junction	Pluggable connection terminal block with screw terminals
Lighting	Durable, homogeneous, white LED call push-button backlighting Invisible, glare-free IR LED night lighting
Protection	Loudspeaker and microphone protected against sabotage