



VE212PN

Enclosure vector,surface mounted,IP65,2x12M,UV-stable,with metric cable entry

Technical Features

Voltage

Nominal voltage	400 - 400 V
Rated operational voltage in DC	1000 - 1000 V

Installation, mounting

Suitable for outdoor usage	Yes
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	No
Has neutral terminal block	No

Capacity

Number of modules	24
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	427 mm
Width	310 mm
Depth	151 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Connection

Number of conduit inlets	12
--------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	No
Has mounting plate	No

Materials

Ultraviolet-resistant	Yes
-----------------------	-----

Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65

Safety	
Locking type	Snap on lock
	Without lock
Glow wire test	850 °C
Sustainability	
RoHS conform	Yes