




WGMR32D1

32A DP SWITCH W/ LED

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Electric current

Rated current	32 A
---------------	------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes