



FL204B

**Polyester enclosure, Orion.Plus, plain door 350x300x160 mm**

**Technical Features**

**Dimensions**

Height	350 mm
Width	300 mm
Depth	160 mm
Thickness of sidewall	2 mm

**Safety**

Ingress Protection (IP) class	IP66
Protection class	Isolation class II
Locking type	3-Side 7 mm Key lock
Impact resistance IK	IK10

**Equipment**

Number of flange plate openings	0
---------------------------------	---

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	Yes

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

**Equipment**

Number of rows	2
----------------	---

**Cover, door**

Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	No
Cabinet door type	Single door

**Electric current**

Rated current	125 A
---------------	-------

**Sustainability**

Halogen free	Yes
RoHS conform	Yes