



8418525

**SCHUKO socket outlet 45°, with screw terminals, Int. module inserts, black matt**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Black
RAL code	9005 9011
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	55.50 mm
Width	55.50 mm
Number of units	1
Built-in depth flush-mounted boxes	32 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP44

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Texts**

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With screw terminals

---

**Suitable for**

integro

---

**Sustainability**

Halogen free

Yes

RoHS conform

Yes

---