



VE18SN

Enclosure,vector,surface mounted,IP65,1x18M,UV-stable,without cable entry

**Technical Features**

**Voltage**

Nominal voltage	400 - 400 V
Rated operational voltage in DC	1000 - 1000 V

**Installation, mounting**

Suitable for outdoor usage	Yes
Mounting on	Surface mounting

**Electric current**

Rated current	63 A
---------------	------

**Equipment**

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No

**Capacity**

Number of modules	18
-------------------	----

**Functions**

With conduit inlets	Yes
---------------------	-----

**Dimensions**

Height	302 mm
Width	418 mm
Depth	151 mm

**Cover, door**

Number of cabinet doors	1
Number of locks	0

**Dimensions**

Number of width units	18
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Connection**

Number of conduit inlets	15
--------------------------	----

**Materials**

Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey

**Equipment**

Has earthing terminal block	No
Has mounting plate	No

**Materials**

Ultraviolet-resistant	Yes
-----------------------	-----

**Safety**

Protection class	Isolation class II
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	850 °C

---

**Sustainability**

---

RoHS conform

Yes