



SN216

Socket 16A 2P+E Fr

Technical Features

Electric current

Rated current	16 A
---------------	------

Voltage

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Light grey
--------	------------

RAL code	7035
----------	------

Dimensions

Height	75 mm
--------	-------

Width	43.75 mm
-------	----------

Depth	61 mm
-------	-------

Number of units	1
-----------------	---

Connection

Connector/plug type	Plug-in terminal
---------------------	------------------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Connectivity

Type of connection	Plug-in connection
--------------------	--------------------

Mounting type	Screw mounting
---------------	----------------

Equipment

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With lock	No
-----------	----

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2.50
-------------------	------

Safety

With enhanced contact protection	No
----------------------------------	----

Ingress Protection (IP) class	IP20
-------------------------------	------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

