



KDN163A

**Insulated busbar 1P 63A fork 10mm<sup>2</sup> 12M**

**Technical Features**

**Electric current**

Rated current 63 A

**Architecture**

Number of poles 1

**Dimensions**

Length 210 mm

**Voltage**

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 415 - 415 V

**Connection**

Cross-section rigid conductor 10 mm<sup>2</sup>

Connector/plug type Phase busbar with fork

**Capacity**

Number of modules 12

**Sustainability**

RoHS conform Yes