



KDN163A

Insulated busbar 1P 63A fork 10mm² 12M

Technical Features

Electric current

Rated current 63 A

Architecture

Number of poles 1

Dimensions

Length 210 mm

Voltage

Rated impulse withstand voltage Uimp 4500 V

Rated operational voltage Ue 415 - 415 V

Connection

Cross-section rigid conductor 10 mm²

Connector/plug type Phase busbar with fork

Capacity

Number of modules 12

Sustainability

RoHS conform Yes