



VE212F

### Enclosure,vector,IP5x, 24M

#### Technical Features

##### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	63 A
---------------	------

##### Equipment

Number of rails	2
Number of rows	2
Number of section in width	1
With lock	No

##### Capacity

Number of modules	24
-------------------	----

##### Functions

With conduit inlets	Yes
---------------------	-----

##### Dimensions

Height	427 mm
Width	310 mm
Depth	151 mm

##### Cover, door

Number of cabinet doors	1
Number of locks	0

##### Dimensions

Number of width units	24
-----------------------	----

##### Cover, door

Door/cover is transparent	No
---------------------------	----

##### Connection

Number of conduit inlets	12
--------------------------	----

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Materials

Material	Polystyrene (PS)
RAL code	7035
Colour	Light grey

##### Equipment

Has mounting plate	No
--------------------	----

##### Materials

Ultraviolet-resistant	No
-----------------------	----

##### Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65
Locking type	Snap on lock Without lock
Glow wire test	750 °C

Sustainability

RoHS conform

Yes