



20261909

Thermostat, change-over contact, centre plate, S.1/B.3/B.7, p.white matt plastic

Technical Features

Architecture

Control/operation element	Rotative
---------------------------	----------

Electric current

Rated current	5 A
Max. switching current	10 A

Voltage

Nominal voltage	230-230 V
-----------------	-----------

Power supply

Supply voltage	230 V AC
----------------	----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Matt
Material	Metal Plastic

Dimensions

Height	71 mm
Width	71 mm
Depth	47.50 mm

Screen

With display	No
--------------	----

Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal
With heater	Yes

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Type of contacts	1x changeover
------------------	---------------

Compatibility

Type of HVAC control	Heating Cooling
----------------------	--------------------

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes