



75664599



B.IQ push-button 4gang thermostat, display, KNX - B.IQ, p. white, matt, plastic

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Functions

With room temperature controller	Yes
----------------------------------	-----

Dimensions

Height	149.20 mm
Width	88.50 mm
Depth	15 mm

Equipment

Number of actuation points	10
----------------------------	----

Controls and indicators

With LED indication	Yes
---------------------	-----

Materials

Colour	Polar white
RAL code	9010
Material	Thermoplastic
Surface finish	Matt

Accessories

Has labelling field	No
---------------------	----

Screen

With display	Yes
--------------	-----

Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function Button help function can be activated
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Protection	With dismantling protection
Temperature	Temperature measurement via internal Temperature sensor and/or external communication object (weighting ratio parameterisable) Provision of the internal temperature value via communication object

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes